# CUSTOM MOLDED HEARING PROTECTION

O O O O BEE

## DECIBULLZ

PRODUCT GUIDE

# FREQUENTLY ASKED QUESTIONS

#### o. HOW DO WE MOLD THEM?

A. Molding Decibullz is easy. Simply heat the molds in a cup of hot water and shape them to your ears. That's it! The Decibullz earpieces can also be re-molded as many times as needed to get the Perfect fit.

#### o. HOT WATER? IS THAT UNCOMFORTABLE?

A. No. Decibullz uses a material that rapidly cools while retaining its pliability. Just wait 30 seconds after re-moving earpieces from the hot water. While the earpieces may feel warm, they will not be hot.

#### Q. CAN THEY BE CLEANED?

A. They are very easy to clean. Simply use soap and cold water and rinse them off or wipe them down with an alcohol wipe.

#### o. HOW DO WE KNOW THEY ARE ACTUALLY NRR 31 / 27 SNR?

A. Our products have had 3rd party testing and are EPA approved.

#### Q. HOW LONG WILL THEY LAST?

A. The molding material will last for as long as you have them. We say they last about 5 years be cause we've only been around for 5 years. The only thing that needs to be replaced are the foam tips which can be bought in bulk.

## Q. WHY WOULD WE PAY MORE FOR DECIBULLZ OVER THE CHEAP FOAM EAR PLUGS THAT SEEM TO WORK FINE?

A. You pay more for a higher end product. Decibullz stay comfortable and secure, ensuring you get the same NRR all day. The initial cost is higher than the standard foam, however you start to see cost savings after the first 4-6 months

#### Q. ARE THEY REUSABLE?

A. YES, Decibullz are reusable. This help cut down on a lot a waste produced by disposable ear plugs

#### o. ARE THEY COMFORTABLE?

A. YES, Decibullz mold to the exact shape of your ear for an all day comfortable fit.

#### o. CAN YOU RE-MOLD THEM?

A. YES, and we are the only ones in the world you can! Unlike fixed molds, Decibullz can be re-molded as many times as needed to get the perfect fit or if your ear shape changes.

#### **Q. CAN I WEAR THEM FOR WORK?**

A. YES. Our products have had 3rd party testing and are certified to EN-352, CE and ANSI standard

## **DECIBULLZ - A FIT AS UNIQUE AS YOU ARE**





**HEAT:** Attach the back plug and smallest silicone tip to one of the molds and drop it into boiling water—one mold at a time. Wait 5 minutes, then safely retrieve with a metal spoon.





**SHAPE:** Allow mold to cool for 30 seconds. Then, insert into ear and gently shape to your unique contour. Leave mold in for 2 min so it retains the new form once removed.



GO: Once you have completed these two steps for the second mold, adjust the silicone tips as necessary, and enjoy. Remold as often as necessary for the perfect fit





**RRP: £29.99** 

AVAILABLE


LANYARD

PLG1-CORD

RRP: £6.99

#### CUSTOM MOLDED PERCUSSIVE SHOOTING FILTERS

#### CUSTOM MOLDED EARPLUGS



Decibullz Custom Molded Percussive Filters protect users from the peak sound pressure of gunshots and explosions while still allowing voice and ambient noise to be heard.

- Impulse and Percussive Noise Protection
- Situational Awareness and Directional Hearing

AVAILABLE IN SIX COLOURS HIGH VISIBILITY Perfect fitting earplugs that will never hurt, never fall out, and provide superior noise

never fall out, and provide superior noise isolation. Perfect for work, shooting, traveling, DIY, loud concerts, musicians, and more!

- Top-Rated NRR 31 / 27 SNR
- Modular to filter products

PLG1-\*\*\*

CIBULL

HEAT AND SHAP

### WHAT IS INCLUDED:

### WHAT IS INCLUDED:





**RRP: £34.99** 

#### **ACOUSTIC TUBE EARPIECE – ISOLATION**

#### **ACOUSTIC TUBE EARPIECE – AWARENESS**

**RTL-RDO-ISO-BLK** 

**RTL-RDO-AWA-BLK** 


**RRP: £34.99** 



**+**ISOLATION CUSTOM MOLDED

Designed specifically for two-way radios, the Decibullz acoustic tube adapter +Isolation help reduce sounds from loud environments so you can clearly hear your radio communication. Custom molded to stay in place and stay comfortable.

- Secure and Comfortable Fit
- Interchangeable with Decibullz Earplugs
- Compatible with Most Communication Systems





**AVAILABLE IN BLACK** CLEAR TUBE NOT INCLUDED

+AWARENESS CUSTOM MOLDED

Designed specifically for two-way radios, the Decibullz acoustic tube adapter +Awareness lets you monitor your radio communications while maintaining situational awareness. Custom molded to stay in place and stay comfortable.

- Secure and Comfortable Fit
- Interchangeable with Decibullz Earplugs
- Compatible with Most Communication **Systems**

1+Awareness

Back Plug

Drawstring

**Carrying Pouch** 

1 Black

Back Plug

5



**RRP: £39.99** 

#### CUSTOM MOLDED HEADPHONES



Decibullz's new and improved Contour ES Custom Molded Contour headphones are easily and quickly molded to the exact shape of your ears to create a perfect fit that will never hurt and never fall out.

The superior noise isolation allows you to focus on what you want to listen to as distracting sounds fade away.

Decibullz Custom Molded Metal Detectable Earplugs feature a EPA certified 31NRR rating and are perfect for manufacturing environments like food processing where contaminant traceability is essential.

**AVAILABLE IN BLUE** 


METAL DETECTABLE

**MOLDABLE EARPIECES** Metal Particles infused into the Custom Moldable Earpieces allow them to be sensed by a metal detector.

CUSTOM MOLDED METAL DETECTABLE EARPLUGS

PLG1-MTLD

The ability to quickly detect PPE that has been lost can prevent costly recalls.



## WHAT IS INCLUDED:

Left and Right Metal Detectable Custom



S, M, L

**Isolation Foam** 



#### CUSTOM MOLDED HIGH FIDELITY FILTERS



The High Fidelity Earplugs have a tuned attenuation. This reduces frequencies to a safer level without distorting the sound. Perfect for concerts, events, sound sensitivity, and anyone wanting to reduce noise while still maintaining sound accuracy.

## **FLTR-PRO-BLK** RRP: £109.99 AVAILABLE LANYARD DECIBULLZ FLTR-LAN-BLK RRP: £7.99 CUSTOM MOLDER HIGH-FIDELITY EA Precision + Pro'

CUSTOM MOLDED PROFESSIONAL HIGH FIDELITY

Decibullz Custom Molded Professional High Fidelity Earplugs have a tuned and flat attenuation. This reduces all frequencies by approximately the same level. Perfect for musicians, professionals, and anyone else who requires extreme sound accuracy.

- SNR value of 17dB offering mid/high Attenuation
- Suitable for music up to 102 dB

#### WHAT IS INCLUDED: Left and Right Left and Right S, M, L S, M, L S, M, L S, M, L EZ Shape EZ Shape **Open Triple Flange Open Triple Flange** Isolation Foam Isolation Foam **Custom Molds** Custom Molds Silicone Tips Silicone Tips DECIBULLZ 7 3 ₹ **High Fidelity Professional Acoustic EVA** Case Acoustic Filters Filters Snapper Case

## WHAT IS INCLUDED:



Custom Moldec	Earplugs					
Part Number	RRP	MASTER	INNER	UPC	Dimensions	Weight
PLG1 - BLK	£29.99	100	20	854843005407	4.29 x 3.03 x 1.54 inch 109 x 77 x 40 mm	1.3 oz 29.2 g
PLG1 - ORG	£29.99	100	20	854843005421	4.29 x 3.03 x 1.54 inch 109 x 77 x 40 mm	1.3 oz 29.2 g
PLG1 - PNK	£29.99	100	20	854843005438	4.29 x 3.03 x 1.54 inch 109 x 77 x 40 mm	1.3 oz 29.2 g
PLG1 - BLU	£29.99	100	20	854843005414	4.29 x 3.03 x 1.54 inch 109 x 77 x 40 mm	1.3 oz 29.2 g
PLG1 - RED	£29.99	100	20	854843005391	4.29 x 3.03 x 1.54 inch 109 x 77 x 40 mm	1.3 oz 29.2 g
PLG1 - GRN	£29.99	100	20	85000614824	4.29 x 3.03 x 1.54 inch 109 x 77 x 40 mm	1.3 oz 29.2 g
CUSTOM MOLD	DED PERCUSS	SIVE FILT	ERS			
FLTR-SHO-BLK	£89.99	50	10	85484300559	4.6 x 5.51 x 1.96 inch 117 x 140 x 50 mm	7.37 oz 209 g
+ AWARNESS A	<b>COUSTIC TU</b>	BE EARP	PIECE			
RTL-RDO-AWA-BLK	£34.99	100	20	850006148561	3.0 x 1.0 3.0 inch 73 x 25.4 x 73 mm	1.2 oz 34 g
+ ISOLATION A	COUSTIC TU	BE EARP	IECE			
RTL-RDO-ISO-BLK	£34.99	100	20	850006148547	3.0 x 1.0 3.0 inch 73 x 25.4 x 73 mm	1.2 oz 34 g
HIGH FIDELITY	ACOUSTIC FI	LTERS				
FLTR-HFE-BLK	£49.99	100	20	85000614803	3.0 x 1.0 3.0 inch 73 x 25.4 x 73 mm	1.4 oz 40 g
FLTR-PRO-BLK	£109.99	50	10	854843005742	4.29 x 3.03 x 1.54 inch 109 x 77 x 40 mm	7.7 oz 216 g
CUSTOM MOLE	DED HEADPH	ONES				
WRD2-BLK	£49.99	100	20	-	3.0 x 1.0 3.0 inch 73 x 25.4 x 73 mm	1.2 oz 34 g
METAL DETEC	TABLE EARP	LUGS				
PLG-1 MTLD	£39.99	100	20	85000614877	Foil — 6.0 x 4.25 x 0.25 inch Foil — 110 x 150 x 15 mm	0.8 oz 23 g

## HOW TO ORDER.

You are welcome to phone in or better still order through our live portal 24/7 at :

## WWW.DCID.UK

Existing Customers – Just log in to place your order

New customers-Please fill in the trade application form and await a call

DECIBULLZ

# **IMPORTANT LINKS**

### - HOW TO ORDER.

You are welcome to phone in or better still order through our live portal 24/7 at :

## WWW.DCID.UK

Decibullz Email; DECIBULLZ@DCID.UK

General Enquires; INFO@DCID.UK

### - MEDIA PORTAL.

Media is everything! In the age of social media, quality images and videos we thought we would give you a head start.

Check out the following portal for all up to date media releases, videos and product imagery you will ever need!

## https://decibullz.canto.com/v/DecibullzUKRetailers

## - <u>FACEBOOK</u>

Find us on Facebook and make sure you give us a "LIKE"

Tag us in your posts using:

@DECIBULLZUK

HASH TAGS :

**#DECIBULLZUK** 

### - INSTAGRAM

Find us on INSTAGRAM and make sure you give us a "FOLLOW"

TAG US in your posts using:

@DECIBULLZ\_UK

HASH TAGS :

**#DECIBULLZUK** 

## - EVENTS and Collaboration

If your having an open day, doing fittings or just want to do some marketing on social media, be sure to let us know. We love to get out and support you when we can!

